



Part names of components of "C4000 Controller"

- ① Case 1
- ② Case 2
- ③ Case 3
- ④ Power indication lamp
- ⑤ Power terminal block
- ⑥ FG terminal
- ⑦ Robot motor connector
- ⑧ Robot signal connector
- ⑨ 7-Segment LED display
- ⑩ Manual switch 1
- ⑪ Manual switch 2
- ⑫ Manual switch 3
- ⑬ Manual switch 4
- ⑭ Select switch
- ⑮ Teaching box connector
- ⑯ RS232C serial communication connector
- ⑰ RS485 serial communication connector 1
- ⑱ RS485 serial communication connector 2
- ⑲ Communication indication lamp
- ⑳ Parallel I/O connector
- ㉑ USB connector (miniB)
- ㉒ Cover
- ㉓ Cooling fan

#### Note

Make sure there are no obstructions near the controller due to the heat release.  
At least 100mm of clearance around the controller (200mm for the upper side) is necessary.  
Make sure the installation accounts for proper heat ventilation issues.

#### Reference drawing

- ✖ This drawing may be revised without any advance notification.
- ✖ When designing the equipment layout based on this drawing, please confirm with JEL in advance.

MODEL 型 式	C4000		
ISSUED NO. 管理番号	WJ0314E	SCALE 尺 度	1/2.5